Triple IFA Roller-Grinder

To enhance performance, you can choose to reduce particle size down to the 500-micron range or increase capacity at the current micron size. Our solutions come in the form of a fully equipped commercial or industrial model, or the addition of a third set to an existing roller grinder, all of which are on par with the IFA conversion. Our products boast solid to the shaft chilled iron rolls, along with a hydraulic roll opener, to ensure quality and easy operation.





- ★ Less Moving Parts
- ★ Hydraulic Roll Opener
- ★ Sample Ports
- ★ Removable Plate Magnets









Scherer Inc.